

Plug socket module Swiss



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 001 0012
Specification	Plug socket module Swiss
HARTING eCatalogue	https://harting.com/39500010012

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket

Version

Termination method	Spring clamp termination
Field of application	Switzerland

Termination data

Supply voltage	250 V AC
Nominal current	10 A
Nominal frequency	50 Hz

Technical characteristics

Conductor cross-section	1.5 mm ²
Mounting depth	30 mm

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	65 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140190450
eCl@ss	27144042 Plug socket
ETIM	EC000450
UNSPSC 24.0	39121406