



- 15A, 125V ac, 10A 250V ac, 3/4 hp 250V ac, TIGL5ACJ to TIGL5FCJ.
  - 15A, 125V ac, 10A, 250V ac, 6A (tungsten), 125V ac, 3/4 hp, 125-250V ac, Cat Nos 2GLC50 to 2GLC55 incl.
  - 15A, 125V ac, 10A, 250V ac, 1 hp, 120-240V ac, 2FA53, 2FA54.
  - 16A, 125V, 8A, 250V, 1 hp, 125-250V, DA280 to DA284, TRDA280 to TRDA284, may have Suffix 00, 01, 05 or 06.
  - 16A, 125V ac, 10A, 250V ac, RA---, RB---, RC---, LRA---, RRG---, with or without suffixes.
  - 16A, 125V ac; 10A, 250V ac; 1/2 hp, 125-250V ac (Codes 23, 93), RA---, RB---, RC---, with or without suffixes, TA25A-PL, TA25B-PL, TA25D-PL, TA25F-PL, with or without suffixes.
  - 16A, 125V ac, 10A, 250V ac, 3/4 hp, 125-250V ac, TA26F-T, 16, RA---, RB---, RRG---, with or without suffixes.
  - 16A, 125V, 10A, 250V, 1 hp, 125-250V, EA260 to EA264, TREA260 to TREA264, may have Suffix 00, 01, 05 or 06.
  - 17A, 125V ac, 12A, 250V ac, TRLA7B, TRLA7D, TRLA7E, TRLA7F, may have Suffix 0 01, 05 or 06.
  - 17A, 125V ac, 12A, 250V ac, 1 hp, 250V ac, 3/4 hp, 125V ac, LTILA70 to 75, LTILB70 to 75, LTILC70 to 75.
  - 17A, 125V ac, 12A, 250V ac, 1 hp, 125-250V ac, TILA70 to 75.
  - 20A, 125-250V ac, TIGC00 to TIGC05.
  - 20A, 125V ac, 12A, 250V ac, 2FA00, 2FA01, 2FA04.
  - 20A, 125V ac, 12A, 250V ac, 1 hp, 120-240V ac, 2FAA00, 2FAA01, 2FAA04.
  - 20A, 125-250V ac, Series 2GA20 to 2GA26, 2GB20 to 2GB26, 2GC20 to 2GC26.
  - 20A, 125V ac, 10A, 250V ac, DA..., DB..., DC...
  - 20A, 125V ac, 10A, 250V ac, 1-1/2 hp, max ratings, Series PA3, PB3, with suffixes.
  - 20A, 125V ac, 10A, 250V, 1/2 hp, 125-250V ac, 215, -A, MAA0A, MM-021.
  - 20A, 125V ac, 10A, 250V ac, 3/4 hp, 125-250V ac, Cat Nos TA22A-T, TA22B-T, TA22F-T.
  - 20A, 125V, 10A, 250V, 1-1/2 hp, 125-250V, EA200 to EA204, TREA200 to TREA204, may have Suffix 00, 01, 05 or 06, CA200, CA201, CA204, CA205, CB200, CB201, CB204, CB205, DA..., DB..., DC...
  - 20A, 125V ac, 15A, 250V ac and optional 3/4 hp, 125/250V ac Series RSC with suffixes.
  - 20A, 125-250V ac, (NI), 15A, 125V ac, 10A, 250V, 3/4 hp, 125-250V ac, TA22-, TB22-, TC22-, LTA22-.
  - 25A, 250V ac; 2FB10, 2FB11, 2FB15, TILA21.
  - 25A, 250V ac, (NI) (30,000 operations) Cat No 2FB310, 2FB311, 2FB315.
- Double-pole:
- 1.5A, 125V ac, .5A, 250V ac, 1A, 28V; Cat Nos 217, -M, -NPP, -NPPA, -PP, -PPA.
  - 3A, 125V, 1A, 250V, 216, 216M, 216NPP, -NPPA, -PP, -PPA, 316, 316M, 316NPP, -NPPA, -PP, -PPA, S316.
  - 2A 250V ac (non-inductive); 5A 125V ac (non-inductive), or 4A, 250V ac; 8A, 125V ac may have 1/4 hp, 125-250V ac or 8A, 14V dc, Series 6 with suffixes.
  - 5A 250V ac, 10A 125V ac, 1/2 hp 125-250V ac, Cat No 2GX10-78XHK with suffixes.
  - 6A, 125V, 3A, 250V, Cat Nos 2BK62, 2BK65, 2BL62, 2BL63.
  - 6A, 125V ac, 3A, 250V ac, Series TIGK36A through TIGK36F.
  - 6A, 125V ac, 3A, 250V ac, 6A, 28V dc, Keylock Type, Series K, (standard version).