

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and self-lubricating properties, reducing maintenance needs.
- **0.79 in Inside and Outside Diameter:** Ensures compatibility with standard shaft sizes, simplifying integration.
- **0.12 in Thickness:** Offers a compact design suitable for space-constrained applications.
- **Dynamic Load Rating of 14 N/mm²:** Supports moderate dynamic loads, enhancing operational efficiency.
- **Static Load Rating of 50 N/mm²:** Handles high static loads, ensuring stability and reliability.

RS PRO Sintered Bronze Thrust Washer, 0.79 in Diameter

RS Stock No: 528-885



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a high-quality sintered bronze thrust washer designed for applications requiring reliable axial load support. With a consistent diameter of 0.79 inches, this thrust washer is ideal for reducing friction and wear in rotating assemblies, providing enhanced durability and performance.

General Specifications

Dynamic Load Rating	14 N/mm ²
Product Type	Thrust Washer
Static Load Rating	50 N/mm ²
Sub Type	Washer

Mechanical Specifications

Inside Diameter	0.79 in
Material	Sintered Bronze
Outside Diameter	0.79 in
Thickness	0.12 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------