



1020

Micro

From small sensitive components to smartphones, protect your gear from the elements in a crushproof, watertight, & dustproof Micro Case from Peli.

- **Available in clear with color liner or solid**
- **Watertight, crushproof, and dustproof**
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Carabiner
- Easy open latch
- Rubber liner for extra protection doubles as o-ring seal
- Peli's legendary lifetime guarantee**
- * Where applicable by law



DIMENSIONS

Interior (L×W×D)	5.31 x 3.56" x 1.68 (13.5 x 9 x 4.3 cm)
Exterior (L×W×D)	6.82 x 4.75" x 2.12 (17.3 x 12.1 x 5.4 cm)
Lid Depth	0.69" (1.8 cm)
Bottom Depth	0.94" (2.4 cm)
Total Depth	1.63" (4.1 cm)
Int Volume	0.02 ft ³ (0.001 m ³)

MATERIALS

Body	Polycarbonate (PC)
Latch	Xylex
O-Ring	Thermoplastic Rubber
Pins	Stainless Steel
Foam	TL - 426 4 lb. Esther
Purge Body	Polycarbonate (PC)
Purge Vent	Polyester Spun-Bond ePTFE Oleophobic

COLOURS

■ Black	■ Black - Clear
---------	-----------------

WEIGHT

Weight With Foam	0.56 lbs (0.25 kg)
Weight Empty	0.55 lbs (0.25 kg)
Buoyancy	0.75 lbs (0.34 kg)
Master Pack Weight	3.96 lbs (1.8 kg)

TEMPERATURE

Minimum Temperature	-10°F (-23.3 °C)
Maximum Temperature	199°F (92.8 °C)

CERTIFICATIONS

IP67

OTHER

Minimum Pack	6
Master Pack	6
Military	yes

ACCESSORIES



1022
Pick N Pluck™ Foam Insert

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 08-19-26