

Features

- Tough, flexible and extremely durable even under cold working conditions.
- Outstanding resistance to the effects of weather.
- Excellent chemical and abrasion resistance.
- RoHS 3 compliant.
- Construction Shock resistant rigid PVC reinforcement & Super flexible Phthalate free PVC

RS PRO Hose Pipes & Flex Tubes

RS Stock No.: 0336786



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A medium weight PVC hose, reinforced with a rigid crush and kink resistant white PVC helix, this hose is tough but still extremely flexible. It has outstanding resistance to the effects of weather. Minimum frictional loss is achieved by the smooth bore.

Key Features:

- Tough, flexible and extremely durable even under cold working conditions.
- Outstanding resistance to the effects of weather.
- Excellent chemical and abrasion resistance.
- RoHS 3 compliant.

Construction:

Manufactured with a white rigid crush and kink resistant anti-shock PVC spiral helix encapsulated in the industry standard olive green flexible PVC cover and smooth inside wall.

Applications:

- Water, slurry, sewage, powders and semi-liquid products
- Agricultural
- Construction
- Manufacturing industries

General Specifications

| | |
|-------------------------------|------------------|
| Hose Pipe / Flexible Tube | Flexible Tube |
| Colour | Green |
| Features | Flexible |
| Series | RS PRO MDS |
| Inner Diameter | 63.5mm |
| Outer Diameter | 73.1mm |
| Material | PVC |
| Hose Pipe Action | Transfer, Vacuum |
| Maximum Working Pressure | 5bar |
| Suitable Application | Industrial |
| Minimum Operating Temperature | -10°C |
| Maximum Operating Temperature | +55°C |
| Length | 10m |
| Reinforced | Yes |
| Bend Radius | 384mm |
| Standards Met | RoHS 3 |
| Vacuum Metres H2O | 9 |