



verso adjustable height workstand with full cupboard. Featuring a robust steel channel, adjustable height framework with 30mm lino worktop. Cupboard size - WxDxH: 525x550x600mm. with single, reinforced door and 1 adjustable height, galvanised steel shelf (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 700x600x780-930mm.

Breite [mm]: 700
Tiefe [mm]: 600
Höhe [mm]: 930
Bruttogewicht [kg]: 53.02
EAN-Code: 5039350119846
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schrank, Gehäuse, Werkbank und EAP

Height adjustment range [mm]	780-930
Worktop/housing top type	Lino
Shelf load capacity [kg]	75
Door type	Plain
Door height 1 [mm]	525