



PRODUCT-DETAILS

EXLT0710

40MM GS-LSZH COAT EX COND 10M - BL



General Information	
Extended Product Type:	EXLT0710
Product ID:	7TCA297120R0143
EAN:	5011949001978
Catalog Description:	40MM GS-LSZH COAT EX COND 10M - BL
Long Description:	Liquid Tight Metallic Conduit, Low Fire Hazard, Conduit Size 40mm, Minimum Bore 35.3mm, Reel Length 10 Meters, Galvanised Steel Core with LFH Coating, Black
Display Name:	EXLT0710

Additional Information	
Product Main Type:	KOPEX-EX FLEXIBLE CABLE PROTECTION
Application:	Connection for Conduit Systems when Low Fire Hazard is Needed

Ordering	
EAN:	5011949001978

UPC: 786210264349

Technical

Number of Batteries:	0
Color:	Black
Material:	Galvanized Steel Core with Low Fire Hazard Coating

Environmental

WEEE Category:	Product Not in WEEE Scope
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units:	1 piece
Package Level 1 EAN:	5011949001978
Package Level 1 Height:	9.37 in 238 mm
Package Level 1 Depth / Length:	19.25 in 489 mm
Package Level 1 Width:	19.25 in 489 mm

Certificates and Declarations

Declaration of Conformity - CE:	9AKK107492A9617
RoHS Declaration:	9AKK107992A8994
REACH Declaration:	9AKK107992A8994

External Classifications and Standards

ETIM 8:	EC001179 - Protective metallic hose
ETIM 9:	EC001179 - Protective metallic hose
UNSPSC:	39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

