

## KombiSIGN 70 / LED Blinking Beacon 843

## LED Blinking light element 24VAC/DC RD



Part No.:	843.110.55		NoHS2	.(ii)	UK
Series:	KombiSIGN 70	 7	<b>КОП</b> 32	t <b>GL</b> ) us	CA

MECHANICAL DATA		
Height	66 mm	
Diameter	70 mm	
Materials	PC	
Dome colour	Red	
Protection category	IP54	
Working temperature minimum	-20°C	
Working temperature maximum	+50°C	
Weight with packaging	83 g	
Product weight	69 g	

ELECTRICAL DATA		
Operating voltage	24V	
Operating voltage type	AC/DC	
Operating voltage frequency	50Hz	
Operating voltage tolerance	+/- 10%	
Rated operational voltage	24 VDC	
Rated operational current	25 mA	
Rated inrush current	500 mA	
Protection class	Protection class 2	
Pollution degree	3	

OPTICAL DATA		
Light source	LED	
Light colour	Red	
Optical signal image	Blink	
Blink frequency (Hz)	1 Hz	
Service life optical	100,000 h maximum	

APPROVAL DATA		
Conforms with CE	Yes	
WEEE	Yes	
Conforms with RED directive	No	
Conforms with ATEX-directive	No	
Conforms with CCC	No	
Conforms with UL	cULus	
UL Type Rating	Type 12	
Conforms with FCC	No	
Conforms with IC	No	
EAC certificate available	Yes	


For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



## KombiSIGN 70 / LED Blinking Beacon 843

## LED Blinking light element 24VAC/DC RD

Conforms with UKCA (Importer)	Yes (WERMA (UK) Ltd.)
Conforms with CMIM	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No
Conforms with VdS	No



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.