

FW75 - Neptune Rigger Boot S5 CI

Collection: Portwest™ Work

Range: Footwear

Material Upper: PVC/Nitrile

Material Outsole: PVC/Nitrile

Product information

A waterproof alternative to the traditional leather rigger. Steel toecap and midsole, fully waterproof, fur lined with side tabs for easy donning.

Standards

EN ISO 20345: 2011 S5
EN 13832-3: 2018



Portwest™ Work

Complete range of styles made of polymeric materials. Durable and waterproof construction that is highly resistant to fuels, oils, grease and fats.

Footwear

Innovation, design, styling and quality components define the Portwest foot protection collection.

Features

- Fur lined for added warmth and comfort
- Kick spur
- Reinforced ankle protection
- Chemical resistant
- 100% Waterproof to keep feet dry
- Cold insulation
- CE certified
- UKCA marked
- Protective steel toecap
- Pierce resistant steel midsole
- Anti-static footwear



FW75 - Neptune Rigger Boot S5 CI
Commodity Code: 6401100000

Test House

Intertek Italia S.p.A. (Notified Body No.: NB: 2575)

Via Guido Miglioli 2/A,

-, Italy

Cert No: LECFI00372281

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
FW75BKR36	Black	44.0	44.0	44.0	1.9300	0.0852	5036108212231	15036108697912
FW75BKR37	Black	44.0	44.0	44.0	1.8800	0.0852	5036108159291	15036108631121
FW75BKR38	Black	44.0	44.0	44.0	2.0100	0.0852	5036108159307	15036108631138
FW75BKR39	Black	44.0	44.0	44.0	1.9800	0.0852	5036108159314	15036108631145
FW75BKR40	Black	44.0	44.0	44.0	2.2400	0.0852	5036108159321	15036108631152
FW75BKR41	Black	44.0	44.0	44.0	2.2600	0.0852	5036108159338	15036108631169
FW75BKR42	Black	44.0	44.0	44.0	2.2000	0.0852	5036108159345	15036108631176
FW75BKR43	Black	44.0	44.0	44.0	2.4100	0.0852	5036108159352	15036108631183
FW75BKR44	Black	44.0	44.0	44.0	2.4200	0.0852	5036108159369	15036108631190
FW75BKR45	Black	44.0	44.0	44.0	2.5600	0.0852	5036108159376	15036108631206
FW75BKR46	Black	44.0	44.0	44.0	2.5900	0.0852	5036108159383	15036108631213
FW75BKR47	Black	44.0	44.0	44.0	2.6700	0.0852	5036108159390	15036108631220
FW75BKR48	Black	44.0	44.0	44.0	2.8600	0.0852	5036108202621	15036108688705
FW75BKR49	Black	44.0	44.0	44.0	3.0000	0.0852	5036108310135	15036108798749

