

Technical sheet

PLAR500AJO


Perforated Road Plate 480 x 480 mm - Thickeness 6 cm


Perforated road plate, 6 cm thick, designed to protect the ground from damage that may be caused by construction and maintenance work while ensuring a smooth and stable passage for heavy vehicles. It also provides stability for equipment installed in construction areas. The perforations allow for better drainage of water and air circulation. It can withstand vehicle weights of up to 40 tons and temperatures ranging from -40 to +60 °C











Customs code	39269097
EAN	3321360109422

Color : Black

Material : Recycled PVC

Specifications :

- Maximum load capacity: 40 T.
- Can be laid directly on the ground.
- Align the interlocking slots to connect and secure the mats.

Length (mm)	Width (mm)	Thickness (mm)	Net weight (kg)
480	480	60	9,00

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com