




**Part Number :** 1731140390  
**Product Description :** FCT Backshell  
Connector Kit, Shielded Plastic Backshell,  
Female Standard Density D-Sub Connector,  
15 Circuits, Straight Cable Outlet, IP67  
Waterproof  
**Series Number :** 1731114  
**Status :** Active  
**Product Category :** D-Sub Connector Kits  
**Engineering Number :** FWH2A-15S-3649




Documents & Resources

Drawings  
[1731140390\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	D-Sub Connector Kits
Series	173114
Description	FCT Backshell Connector Kit, Shielded Plastic Backshell, Female Standard Density D-Sub Connector, 15 Circuits, Straight Cable Outlet, IP67 Waterproof
Contact Type	Machined Solder
IP Rating	IP67
Magnetic	Yes
Product Name	FCT Products
Type	Plastic, Standard Density
UPC	191130516728

### Electrical

Current - Maximum per Contact	7.5A
Shield Type	Shielded Plastic
Shielded	Yes

### Physical

Cable Diameter	6.00-8.00mm
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Red
Durability (mating cycles max)	500
Gender	Female
Material - Backshell	Polyester
Material - Contact	Brass
Material - Resin	PBT
Material - Screw	Brass

Material - Seal	Elastomer
Material - Shell	Brass
Mounting Style	Locking Screw
Net Weight	25.000/g
Number of Rows	2
Orientation	Straight
Packaging Type	Bag
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Backshell	Nickel
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Plating min - Termination	0.100µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-25° to +70°C
Termination Style	Solder Cup
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Size (AWG)	20