



Part Number : [460550007](#)


Product Description : Mini-Fit H2O Crimp Terminal, Female, with Tin (Sn) over Nickel (Ni), UL1015, 20-18 AWG, Loose

Series Number : 46055

Status : Obsolete

Product Category : Crimp Terminals

Packaging Alternative : [460550005](#) (Reel)




Documents & Resources

Drawings

[PK-5556-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Crimp Terminals
Series	46055
Description	Mini-Fit H2O Crimp Terminal, Female, with Tin (Sn) over Nickel (Ni), UL1015, 20-18 AWG, Loose
Application	Power, Wire-to-Wire
Comments	UL1015 18-20 AWG
Product Name	Mini-Fit H2O
UPC	883906938222

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.147/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.52mm / 2.81mm
Wire Size (AWG)	18, 20
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Male and Female Crimp Terminals, 20-18 AWG Wire	<u>638191800</u>

This document was generated on Aug 08, 2025

Obsolete