



9007A

LIMIT SWITCH LEVER ARM HEAD C



[Download your 9007A datasheet](#)



[Characteristics](#) | [Documents & Downloads](#)

Main [-] Hide

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch head
Device short name	9007C
Head type	Rotary head
Product compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Rotary
Type of operator	Zinc spring return without operating lever (low differential)
Type of approach	1 or 2 programmable direction lateral approach
Positive opening	Without

Complementary [-] Hide

Switch actuation	From left and right CW and CCW
Product weight	0.41 lb(US)

Environment [-] Hide

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

Offer Sustainability [-] Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available download Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty [-] Hide

Period	18 months
---------------	-----------

