

## 135A - LIGHT ALLOY 90° OFFSET AMERICAN MODEL PIPE WRENCHES | 135A.18



### Description

- Capacity: 0 to 76 mm; 0 to 2"1/2.
- Light alloy body.
- Jaws in steel hardened to 55 HRc.

### Information

A maxi ["]	2
A maxi [mm]	60
C [mm]	39
E [mm]	39
L ["]	39
L [mm]	450
[kg]	1,480

