SIEMENS

Data sheet 8WD5320-0CD

Integrated signal lamp, single flash light, w. built-in electronic flash, yellow, 24 V DC, diameter 70 mm

Figure similar

General technical data	
Product designation	Flashlight element
Consumed current maximum	125 mA
Type of voltage	
• of the operating voltage	DC
Operating voltage	
• 1 at DC rated value	24 V
Relative positive tolerance of the operating voltage	10 %
Relative negative tolerance of the operating voltage	-10 %
Reference code	
• acc. to DIN EN 81346-2	P
Mounting type	Bayonet / flush mounting
Color	yellow

Mechanical data	
Product component Light source	Yes
Type of electrical connection	screw-type terminals
Outer diameter of the signal column element	75 mm

Subject to change without notice
© Copyright Siemens

Lamp

Design of the optical signal	flash light
Type of light source	Xenon gas discharge lamp
Light intensity	35 796 cd
Flash frequency	1 Hz
Number of flashes of light element	4 000 000

Ambient conditions

Ambient temperature during operation	-20 ... +50 °C
Protection class IP	IP65
Depth	31 mm
Height	66 mm
Width	75 mm

Certificates/approvals

General Product Approval	EMC	Declaration of Conformity	other
UL EAC C-Tick EG-Konf.			Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5320-0CD

Cax online generator
http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5320-0CD

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/8WD5320-0CD

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5320-0CD&lang=en

Subject to change without notice
© Copyright Siemens



SIEMENS

last modified: 11/09/2018

Subject to change without notice
© Copyright Siemens