



182.72.104.66LR52Laufrollen

# Track rollers LR5204-2Z-TVH-XL (Series LR52)

double row, sealed on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

d	20 mm
D	52 mm
C	20,6 mm
d2	29,2 mm
R	500 mm Crowning radius
rmin	1 mm
m	0,23 kg Mass
Cr w	16900 N Effective dynamic load rating as track roller (radial)
Cor w	12300 N Effective static load rating as track roller (radial)
Fr per	10200 N Permissible dynamic radial load
Cur w	640 N Fatigue limit load
nD G	7300 1/min Speed (with continuous operation and grease lubrication)

