


EXP-A921/07/P Datasheet

 [View Product Page](#)

Product Name // **Inline Cable Connector Large Cable EXP-A921 Series 7 Contact Plug 20mm-22mm Cable (Yellow Gland)**



// **Product Description:**

- Inline Cable Connectors for hazardous areas
 - Water and dustproof to IP68 when mated with compatible connector
 - Positive fast-acting locking ring - can be turned with a gloved hand
 - Plug or Socket
 - 2, 3, 4, 5, 7, 10 Contact with leading Earth on 3, 4, 5, 7 Contact versions, trailing Neutral on 5 Contact version
 - Screw Terminals
- Choice of cable acceptance 7mm-22mm diameter depending on part code (see data for details):
 - EXP-09 part codes 7mm-15mm diameter
 - EXP-A9 part codes (large cable version with strain relief clamp) 14mm-22mm diameter
 - Packs of Cable Glands for differing cable diameters available separately (EXP-0980, EXP-A980)
 - EXP-0991 heavy duty Sealing Cap available separately to maintain IP rating of unmated connectors
 - Mate with EXP-09 or EXP-A9 Series Flex and Panel Mount Connectors, as appropriate

// **General Information:**

Product Display Title:	Inline Cable Connectors for hazardous areas
Product Family:	Circular Power Connectors
Product Series:	EXPlora
Approvals:	UL
Body Material:	Polyester (PET)
Body Material Type:	Plastic Body
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	16A
Diameter Over Coupling Ring Mm:	58mm
Flamability Rating:	UL94V-0
Function:	Inline Cable Connector
Ip Rating:	IP68
Max Cable Entry Size:	22mm
Min Cable Entry Size:	20mm
Max Contact Accomodation Awg:	14AWG
Min Contact Accomodation Awg:	10AWG
Max Contact Accomodation Mm2:	4mm2
Min Contact Accomodation Mm2:	2.5mm2
Max Operating Temperature:	+55°C
Min Operating Temperature:	-20°C
Number Of Contacts:	7 Contacts
Voltage Max:	430V

// **Product PDF Links**



// **Product 3D CAD Model Links**

