

# KING'S K2 RANGE



KING'S

The Logical Choice

## K2 High-cut Rigger Boot



**Description:** Brown Grain High-cut Leather Boot

**Size:** UK 3-13 | US 4-14 | EU 36-48

**Industries:** Construction, Mining, Manufacturing, Heavy and General Industries, Utilities, Oil and Gas, Transportation, Logistics

**Standard:** SRC (EN ISO 20345:2011)



SKU	Toecap	Steel Midsole	Color	Outsole	Category
TE2005K	Yes	Yes	Brown	Single density PU	SB
TE2005KX	Yes	No	Brown	Single density PU	SB

Engineered for the rigors of craggy, foundry, and quarry work environments, the K2 range of safety footwear delivers exceptional protection and comfort from heel to toe. Its rubber outsole offers outstanding resistance to extreme temperatures (up to 300°C), as well as oils, acids, and alkalis, all while maintaining a lightweight feel for user comfort.

The King's K2 Range features a contoured EVA cushion insole that enhances moisture absorption while providing exceptional shock cushioning. This ensures longer-lasting freshness for your feet and greater comfort, even during extended hours of wear.

### Features:

- Designed for tough environments - ideal for craggy, foundry, or quarry work environments.
- High-cut rigger boot featuring a brown grain leather upper.
- Quick and easy donning and doffing.
- Features a lightweight and soft contoured EVA cushion insole that offers exceptional breathability and moisture absorption for longer-lasting freshness, along with shock cushioning to enhance foot comfort.
- Rubber shoe sole engineered to resist extreme temperatures (up to 300°C), oils, acids, and alkalis, while maintaining lightness and comfort.

- Excellent slip resistant sole delivers durable traction; SRC (EN ISO 20345:2011); Anti-static.
- Sole resistant to oils and acids/alkalis.

### Industry Applications:

- Recommended for indoor/outdoor works. Suitable for heavy and general industries.

### Storage And Care:

- Footwear should be stored in their original packaging. Keep in an area that is not subject to rapid changes in temperature or humidity levels.

### Care Instructions:

- Store shoes in a cool, dry and well-ventilated area after use.
- Remove excess dust or dirt with a brush.
- Remove any marks using a damp cloth and soap if necessary. Polish any grain or pigmented leathers using a commercially available shoe care product.

### SOLE FEATURES



Puncture Resistant



Anti-Static



Slip Resistant



Heat Resistant Sole (300°C)



Mineral Oils Resistant



Organic Oils & Fats Resistant

### TOECAP FEATURES



Steel Safety Toecap

### COMFORT FEATURES



Wide Profile Toecap



Lightweight

King's Safety Footwear  
Asia Pacific Headquarters  
Level 25, UOA Corporate Tower Lobby B,  
Avenue 10, The Vertical  
59200 Bangsar South City  
Kuala Lumpur, Malaysia

+603-2777 3948

hsp.asean@honeywell.com

www.pip-hsp.com

LEARN MORE



KING'S K2\_TE2005K | v01/25  
© 2025 PIP | HSP