



Part Number : [1200798054](#)
Product Description : Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Black PUR LSOH Cable, 2.0m (6.56') Length
Series Number : 120079
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : W04000H09M020



Documents & Resources

Drawings
[1200798054_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120079
Description	Ultra-Lock (M12) Single-Ended Cordset, 4 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Black PUR LSOH Cable, 2.0m (6.56') Length
IP Rating	IP69K
Product Name	Ultra-Lock (M12)
Protocol	EtherNet
Type	Single Ended
UPC	78172533029

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	4.70mm (.185")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Ultra-Lock (M12)
Connector End B	Pigtail
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PUR

Material - Connector Body	TPU
Material - Contact	Bronze
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	FPM
Material - Plating Mating	Gold
Net Weight	78.800/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	UL 21198, LS0H
Wire Size (AWG)	22