

product type designation

IWLAN RCoax connector N-Connect Female N-Connector
 RCoax N-Connect female N-connector 2.4 and 5 GHz Can be assembled in the field; Connection piece of RCoax Cable for connection of further components



electrical data

number of electrical connections	1
type of electrical connection	N-Connect female
transmission frequency	0 ... 6 GHz
impedance	50 Ω

ambient conditions

ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +85 °C
<ul style="list-style-type: none"> during storage 	-40 ... +85 °C
<ul style="list-style-type: none"> during transport 	-40 ... +85 °C
protection class IP	IP67

design, dimensions and weights

diameter	27 mm
length	65 mm
net weight	159 g

standards, specifications, approvals

certificate of suitability	
----------------------------	--

- RoHS conformity

Yes

further information / internet-Links

Internet-Link

- to website: TIA Selection Tool
- to website: Selector TIA Selection Tool
- to the website: IWLAN
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool>
<http://www.siemens.com/snst>
<http://www.siemens.com/iwlan>
<http://www.siemens.com/simatic-net>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

last modified:

10/05/2020