

FEATURES

- Pozidriv head type for improved screwdriver grip
- Pan head design for a flat bearing surface
- A4 316 Marine Grade stainless steel
- Easily cleanable
- Meets DIN 7985 Standards

RS PRO, M4 Pan Head, 12mm Stainless Steel Pozidriv A4 316

RS Stock No.: 190-507



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO a high-quality pan head machine screw with a versatile Pozidriv recess for a superior grip when tightening. This machine screw has a metric thread and is made from high quality A4 stainless steel which has excellent corrosion resistance. Grade 316 steel is also known as marine grade stainless steel due to its increased resistance to chloride corrosion making it ideal for use in marine applications.

General Specifications

Head Shape	Pan
Drive Type	Cross
Applications	Swimming pools, Chemical plants, Boat deck fittings, Dairy equipment, Medical sterilising equipment, Sewerage treatment plants

Mechanical Specifications

Thread Size (Metric)	M4
Length Metric	12mm
Material	Stainless Steel
Stainless Steel Type	A4 316
Finish	Plain
Thread Pitch	0.7mm
Specification	DIN 7985



RS Part No.	Thread Size	Length
190484	M4	8mm
190490	M4	10mm
190507	M4	12mm
190513	M4	16mm
190541	M5	10mm
190563	M5	16mm
190579	M5	20mm
190585	M6	10mm
190608	M6	16mm
190614	M6	20mm
190636	M6	30mm
528693	M2	6mm