

2154SK 8

3C-Screwdriver with striking cap

for slotted head screws

Code	ETIM
1845241	EC000158
EAN	UNSPSC
4010886857229	27-11-17-01
Country of origin	eCl@ss
Slovenia	21-04-04-01
Customs tariff number	
82054000	



Article description

- Acc. to DIN ISO 2380-2, cutting edge according to DIN ISO 2380-1 Form A
- 3-component Power-Grip³ handle with impact cap
- Ergonomic handle shape for accurate, non-tiring work
- Positive-fit joint of handle and blade for optimum transmission of force
- Hexagon blade with additional hexagon bolster
- Blade of galvanised molybdenum-vanadium steel

Article information

Contents (Qty of pieces)	1	Impact cap	yes
Net weight [kg]	0,178 kg	Cap rotatable	no
Total length [mm]	275 mm	Anti-magnetic	no
Total width [mm]	40 mm	Ball head	no
Total height [mm]	32 mm	Handle available	yes
Material	Molybdenum-vanadium-steel	Isolated	no
Drive connector hexagon male (metric)	13,0 mm	Corrosion Protected	no
Blade length	150 mm	Colour coding	no
Standard	DIN ISO 2380-2	Unit-tested	no
Blade width [mm]	8,0 mm	Handle design	3C
Low sparking design	no	Output tip reference standard	DIN ISO 2380-1 - Form A
Blade shape	Hexagon	Drive hexagon	yes
Roll protection	no	Blade thickness	1,2 mm