

Lawn Mower XGT®

LM003G

40Vmax, 380 mm

Model LM003G is a 380mm (15") lawn mower powered by 1 x XGT® Li-Ion battery.

Features and Benefits: Cutting, Collecting, Mulching, High mowing performance, Warning lamp for battery capacity, high temperature and overload, Deck material plastic.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3800 min ⁻¹
Cutting height positions	8
Width of Mowing Deck	38 cm
Mowing Height	20 - 75 mm
Rear Wheel Diameter	16,5 cm
Front Wheel Diameter	14 cm
Actual mowing area 8,0 Ah	780 m ²
Cumulative	✓
Bio cutting	✓
Continuous Use XGT® 40V Max / 8.0 Ah	48 min
Collecting Box Capacity	40 L
Sound Power Level (L _{WA})	90 dB(A)

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Related products

■ Optional AC

1913G8-3
Blade 380 Set



1913H0-6
Mulching Blade 380mm



1913H2-2
Mulching Plug 380 Set



■ Other

User manual

Parts drawing