

- Multi-Tone Sounder in combination with Xenon Flash
- Optical and audible signal can be triggered separately
- Choice of different 8 tones
- Adjustable sound output
- Easy to mount
- High protection rating IP 65



Mounting holes integrated into the product rim allow easy mounting without having to remove the dome.

#### TECHNICAL SPECIFICATIONS:

<b>Dimensions</b> (Diameter x Height):	89 mm x 100 mm
<b>Housing:</b>	PC, black
<b>Dome:</b>	PC, transparent
<b>Connection:</b>	Screwable connection with wire protection max. 1.5 mm <sup>2</sup>
<b>Cable entry:</b>	Membrane cover up to Ø 9 mm
<b>Flash energy:</b>	1 Ws
<b>Flash frequency:</b>	1 Hz
<b>Sound output:</b>	max. 100 dB
<b>Fixing:</b>	Base mounting
<b>Life duration:</b>	4 x 10 <sup>6</sup> flashes

#### ORDER SPECIFICATIONS:

	24 V ≅
red	421 120 75
yellow	421 320 75

Available from September 2005

#### TONE TYPES AND FREQUENCIES:

Tone A No.	Tone type
1	Horn tone (c. 200 Hz)
2	Continuous (c. 2.3 KHz)
3	1 Hz tone (c.2.3 KHz)
4	20 Hz whistle tone (c. 2.3 KHz)
5	800-970 Hz rising @ 1 Hz
6	2400-2850 Hz rising @ 7 Hz
7	1200-500 Hz falling @ 1 Hz
8	Alternating tone

