



ORBITAL SANDER 150MM-5VU

RC92461S

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:13:15





DESCRIPTION

ORBITAL SANDER 150MM-5VU

The new RC92461S greaseless sander stands out for its ergonomic design and the maximum power that can be achieved thanks to advanced engineering. The greaseless mechanism and low air consumption of just 57 l/min also help to protect the environment. The special design ensures optimum sanding finish and maximum machine life. The machine has an eccentric movement diameter of 5 mm and is equipped with a new 15-hole sanding pad, so that in theory all types of sanding paper can be used (6, 7, 8 or 15-hole sanding paper).

SPECIFIC DATA

Designation	ORBITAL SANDER 150MM-5VU
Sales reference	RC92461S
L (mm)	210

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



Weight (g)	700
l (mm)	150
h (mm)	100
Power (W)	180
Rotation speed (rpm)	12 000
Vibration (m/s ²)	1,5
Noise level (dBa)	84
C mm	6,3
C min mm	170
C mm	1/4
Eccentricity (mm)	5
Tray Ø (mm)	150
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

