

Datasheet

130mm Stainless Steel Flat Nose Pliers

RS Stock number [536-341](#)



Specification:

- Material: Stainless steel sheet (#420-j2) for plier, pivot, spring steel for tension return spring, PVC injection handle
- Finish: Grinding-vibration finish for plier, chrome plated rivets, blue colour handle
- Hardness: Heat treated to hrc:46~50(body) pivot--hrc:20~25

Contents:

1pc- 5" stainless long flat pliers with lightweight return coil spring and blue colour vinyl handle(overall length- 130mm,thickness od steel sheet--3.0mm,25mm long tapering serrated jaw and non-toxicant insulated soft handle)

Remarks:

Hardness and serrated function tests are required