






Terminal, spring-loaded terminal, three-tier, PE/L/L, 2.5 mm², gray



Model	
product brand name	SENTRON
product designation	Terminal blocks
design of terminal terminal levels internally linked	No
operating voltage rated value	500 V
Protection class	
combustibility class according to UL 94	V0
Main circuit	
operational current rated value	22 A
Appearance	
color	grey
Product details	
product component required end cover plate	Yes
Number	
number of terminal levels	3
number of terminal points per terminal level	2
Connections	
connectable conductor cross-section solid	
• minimum	0.08 mm ²
• maximum	4 mm ²
connectable conductor cross-section finely stranded	
• with core end processing minimum	0.14 mm ²
• with core end processing maximum	2.5 mm ²
• without core end processing minimum	0.08 mm ²
• without core end processing maximum	2.5 mm ²
type of connection 1	spring-loaded terminal
type of connection 2	spring-loaded terminal
position of the terminal	top
Mechanical Design	
height	99.48 mm
height with lowest-profile installation	58 mm
depth	56.45 mm
length	99.5 mm
fastening method	TH35 DIN rail
net weight	20 g
material of the insulating body	Other
Environmental conditions	
ambient temperature during operation	
• minimum	-60 °C
• maximum	105 °C

Approvals Certificates

General Product Approval	Declaration of Conformity	other
 Confirmation	 Confirmation	 Confirmation  Miscellaneous

Environment

[Environmental Confirmations](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mifb=8WH2030-4HF00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WH2030-4HF00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mifb=8WH2030-4HF00

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

7/19/2023 