

Datasheet

# RS Pro LED Long Reach Task Lamp CRI 90

RS Stock No: 183-5233



## Product details:

A professional long reach task lamp with slimline design and swivel head, perfect for lighting up narrow spaces or turning 90° for an even spread in a wide area. Featuring an inbuilt dimmer switch for complete lighting versatility and the right balance of light for any environment.

## Features & Benefits:

- 90 white SMD LEDs producing 6000 - 7000K light
- Improved colour rendering with 90 CRI
- Energy efficient, using only 14w
- LEDs never need replacing
- Shadow free, cool light
- Shadow free, cool light that cuts glare and helps reduce eye strain and headaches
- Built-In dimmer switch providing a balance of light to suit any task
- Ergonomic design with swivel head able to reach narrow spaces
- Sturdy joints and covered arm for secure, steady lighting and easy positioning
- Includes table clamp
- Dual UK & EU Plug Options