



## Main

Product range	Mureva BOX
Product type	Junction box
Colour	Grey (RAL 7035)
Quantity per package	1 piece

## Complementary

Mounting	Surface
Cable entry	Knock-out
Fixing mode	Screw-fixed: cover
Interior dimensions	175 x 150 x 80 mm
Number of cable entries	8 x M12/16 4 x M20/25 2 x M25/32
Material	PP (polypropylene): body and cover
Electrical insulation class	Class II conforming to IEC 536
Height	90 mm
Width	195 mm
Depth	165 mm
Net weight	0.38 kg

## Environment

Operating temperature	-25...40 °C
IK-Class	IP55 conforming to IEC 60529
IK-Class	IK07 conforming to EN 50102
Glow wire temperature	750 °C
Standards	EN 60670 CE
Environmental characteristic	Halogen free

## Packing Units

Package 1 Weight	0.380 kg
------------------	----------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------