



Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 2 / 9.7; Upri(V): 400-230+/-15; Usec(V): 2x115; Isec(A): 2x8.7; F(Hz): 50...60; vector group/shielding winding: II0 /0; temperature rise/insulation class: 40 /B; IP00; connection: screw/flat-type connection; mounting: screws; EN 61558-2-1, -2-2, -2-4 >UL/CSA-recognized< >control transformer< >isolation transformer<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	2 000
efficiency		0.96
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	9 700
relative short-circuit voltage	%	1.9
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	415
• _2 rated value	V	400
• _3 rated value	V	385
• _4 rated value	V	245
• _5 rated value	V	230
• _6 rated value	V	215
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	230
• _2 rated value	V	115
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00

Mechanical data		
type of electrical connection		screw-type terminals / tab terminals
- at output for main current circuit - at input for main current circuit		screw-type terminals / tab terminals
fastening method		screws
construction form of the iron core		EI 174/102
width	m	0.176
height	m	0.164
depth	m	0.158
Certificates/ approvals		
General Product Approval	other	Environment
   	Confirmation	Environmental Confirmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information for data generation and storage https://support.industry.siemens.com/cs/ww/en/view/109995012 Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM6442-8JD40-0FA0 Cax online generator https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM6442-8JD40-0FA0 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/4AM6442-8JD40-0FA0 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM6442-8JD40-0FA0&lang=en

last modified:

4/2/2025 