

METAL SAFETY QUICK COUPLINGS - CSM 11

Hose tail coupler

Profile : ISO 6150C



Part number	For hose ID (mm)	Min. operating pressure (bar)	Flow rate at 6.00 bar (l/min) ($\Delta P = 0.60$ bar)	ID passage (mm)	Temperature min/max (°C)
CSM 111813	13 mm	2.00 / 16.00	4120.00	11 mm	-15.00 / 70.00
CSM 111819	19 mm	2.00 / 16.00	4120.00	11 mm	-15.00 / 70.00

Part number	Dim. A (mm)	Dim. B (mm)	Dim. C (mm)
CSM 111813	112.00	33.00	30.00
CSM 111819	147.00	33.00	30.00

