



### Main

Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	Easypact CVS PowerPact Multistandard Compact NSX
Voltage release type	Undervoltage release
[Uc] control circuit voltage	220...240 V AC 208...277 V AC

### Complementary

Threshold tripping voltage	0.35...0.7 x Un - during opening time 0.85 x Un - during closing time
Supply holding power	5 W
Supply inrush power	30 W
Mounting mode	Fixed
Response time	50 ms
Auxiliary connection terminal	Screw terminal 0...1.5 mm <sup>2</sup>

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0835 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product environmental</a>
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---