


				REVISIONS			
2008/04/08	C	Revise Item&Part NO. &Add 15M	TOM				
2008/05/16	D	Revise Part NO.	TOM	DATE	LTR	DESCRIPTION	APVD
2008/05/21	E	Revise HDMI Molding Spec	TOM	2008/01/03	A	New Drawing.	TOM
				2008/01/17	B	Add specifications	




Note: 1.HDMI-19P Mould No.:DM $\frac{1}{2}$ -H1011.  
 2.DVI-(18+1)P Mould No.:DM $\frac{1}{2}$ -H591  
 3.DVI-(18+1)P One Side Molding LOGO" ",  
 Other Side Molding Blank LOGO.  
 4.RO=RoHS.

specifications:  
 1.bandwidth up to 5 Gbps  
 2.10,000 Cycles  
 3.Gold-plated contacts  
 4.Lead-Free plating  
 5.Tray and embossed packaging  
 6.Current: 0.5A  
 7.Voltage:40V

Table:

PART NO	ITEM NO	LENGTH
489-406	P-A6C068-6-AL10M	10000±100
489-438	P-A6C068-6-AL15M	15000±150



*New mold*



15	NA360030	Paper Tape	Paper Tape.Single Side With Adhesive.W12*L130mm-RO
14	NA360030	Paper Tape	Paper Tape.Single Side With Adhesive.W12*L100mm-RO
13	GC300160	Copper Foil	Copper Foil.W30*L70mm-RO
12	GC300160	Copper Foil	Copper Foil.W30*L60mm-RO
11	JA860020	H.S.T	Black Heat Shrink Tube OD:1.5mm-RO L:10mm
10	JA860870	H.S.T	Black Heat Shrink Tube OD:0.8mm-RO L:15mm
9	JA860380	H.S.T	Black Heat Shrink Tube-RO.φ2.5*L8mm
8	GC330030	Stick	Tin Stick-RO
7	NA002640	Screw	DVI Thumb Screw 2.8*32mm-RO #4-40UNC Black
6	JB513960	PVC	PVC 45P-RO Black(T-000)
5	J1190010	PE	Transparent PE-RO
4	GC340080	Tin	OD:0.6mm-RO
3	1B370070	Conn.	DVI-(18+1)P-N-GS-K-S-RO Black Insulator.Solder Type.Shell Plated Nickel
2	1J280210	Conn.	HDMI-19PSGS4-K-A-RO W/PCB Shell Plated Nickel.Contact Gold Plated 15u"
1		Cable	UL20276 (1P#24+AL+D+MYLAR)*4C+1P#24+5C#24-RO+AL+B OD9.5 Black(T-000) Lcm
No	Part No	Title	Description

UNLESS OTHERWISE SPECIFIED TOLERANCE : X. ±0.2 ANGLES : ±2° X.X ±0.1 X.XX ±0.05 DO NOT SCALE DRAWING				TITLE		OEM CABLE ASSEMBLY		C3110	
DRAWN BY		Jack		SIZE A	UNIT MM	PART NO. 489-4XX		REV. E	
CHECKED BY				SCALE	THIRD ANGLE PROJECTION		PAGE 1 OF 1		
APPROVED BY				DATE		ITEM NO. P-A6C068-6-ALXXM		05/21/2008	
DWG NO.		G489-4XX							