



LOGO!230RCE, LOGIC MODULE, DISPL. PU/I/O:
 115V/230V/RELAY,
 8 DI (4AI)/4 DO;
 MEM 400 BLOCKS EXPANDABLE,
 ETHERNET BIULD IN WEB-SERVER,
 DATALOG STANDARD MICRO SD CARD FOR LOGO!
 SOFT COMFORT V8 PREVIOS PROJECT USABEL

Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide
Supply voltage	
115 V DC	Yes
230 V DC	Yes
permissible range, lower limit (DC)	100 V
permissible range, upper limit (DC)	253 V
115 V AC	Yes
230 V AC	Yes
Time of day	
Time switching clocks	
Number	8
Power reserve	480 h
Digital inputs	
Number of digital inputs	8
Digital outputs	
Number of digital outputs	4 ; Relays
short-circuit protection	No ; external fusing necessary

Relay outputs	
Switching capacity of contacts	
with inductive load, max.	3 A
with resistive load, max.	10 A
EMC	
Emission of radio interference acc. to EN 55 011	
Emission of radio interference acc. to EN 55 011 (limit class B)	Yes
Degree and class of protection	
IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
Developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
Marine approval	Yes
Ambient conditions	
Operating temperature	
Min.	0 °C
max.	55 °C
Dimensions	
Width	71.5 mm
Height	90 mm
Depth	60 mm
Status	Sep 8, 2014