



My Cloud™ Pro Series PR4100

Pre-configured NAS, Diskless NAS

Product Specifications	Average latency	NA
	Average read seek	NA
	Battery	Yes
	Cache/Buffer	NA
	Data transfer rate	NA
	Disk Capacity	0TB, 8TB, 16TB, 24TB, 32TB, 40TB, 56TB
	Drive Bays	4
	Interfaces	USB 3.0 x 3
	Memory	4 GB DDR3L (expandable to 16 GB with two 8 GB DDR3L SO-DIMM)
	Processor	Intel Pentium N3710 1.6 GHz (Burst speed up to 2.56 GHz)
	Rotational Speed	NA
	Tape Drive	NA
	Write Speed	NA
Product Dimensions	Length	9.13 in (232.00 mm)
	Width	6.69 in (170.00 mm)
	Height	7.56 in (192.00 mm)
Product Weight	Weight	32TB 13.27 lb (6.02 kg)
Colors available		Black
Country Code / Origin		Product of Thailand, Malaysia, or China
Environmental Specifications	Operating Temperature	0°C to 35°C
	Non-op Temperature	-40°C to 70°C
Power Specifications	AC input voltage (AC adapter)	100-240 VAC
	AC input frequency	50-60 Hz
Languages for software		<ul style="list-style-type: none"> • English • Chinese, Simplified • Chinese, Traditional • Czech • Dutch • French • German • Hungarian • Italian • Japanese
Languages for User Manual		<ul style="list-style-type: none"> • English • Arabic • Indonesian • Chinese, Simplified • Chinese, Traditional • Czech • Danish • Dutch • Finnish • French • German • Greek • Hungarian • Italian • Japanese • Korean • Norwegian • Polish • Portuguese-Brazilian • Romanian • Russian • Slovakian • Spanish-Int'l • Swedish • Turkish
Licenses Included		NA
Limited Warranty²	Worldwide	Populated Unpopulated
Previous Product Model	Product Name	NA
	Ref Order Number	NA
Regulatory	NRCAN compliant	NA
	RoHS compliant ¹	Yes
Software Included		My Cloud OS:

*Download WD My Cloud mobile app from iOS and Android app stores.

¹WD complies with the Restriction of Hazardous Substances (RoHS) Directive 2002/95/EC of the European Parliament, which is effective in the EU beginning July 1, 2006. RoHS aims to