

KYBKM-90BHMTU Stainless steel mini keyboard with Function keys & trackball - Hole mount



Faceplate Dimensions(W X H): 392×135 mm

Basic Instruction :

1. Support OS: Windows XP/Vista/7/8 and above, Linux and Unix
2. comply with ISO/IEC 9995、 GB/T14081 standard
3. Keyboard made of high quality stainless steel
4. Dustproof, waterproof, shake-proof and vandal proof

Applications:

Check-in Kiosk, Boarding Kiosk, Info-Kiosk, Internet Kiosk, Medical Kiosk, Industrial Control Platform.

Interfaces PS/2 or USB

Mechanism Performance :

1. Keyboard lifespan: more than 2 million
2. Force on keys: 3-5N
3. Key travel: >2.5mm
4. Diameter of trackball: 38mm

Environment adaptation :

1. Protection Level: IP65 static /IP54 dynamic
2. Operating Temperature:
Economical Grade: 0℃~+45℃ RH:30~90%
Industrial Grade: -40℃~+60℃ RH: 30~90%
3. Storage temperature(Recommended): -25℃~+55℃ RH:20~95%(No condensate)
4. Maximum humidity in operating environment:90%
5. Air Pressure: 60-106 Kpa

Approvals:

RoHS, CE, FCC
IP65, IK07