



150-12

E0845086

Cable Lug KRF, 150mm², M12



Product Properties:

Suitable for Class 5 conductor	Yes
Suitable for Class 6 conductor	Yes
Insulated	No
Max. current (I _{max})	395 A
Number of mounting holes	1 .
Flange shape	Ring shape
Colour insulation	Other
Slender flange model	No
With sight-hole	Yes
Conductor category	Several
Max Temp	150 °C
Surface protection	Tinned
Material	Copper
Connecting angle	180° (horizontal)
Series	KRF/KSF (10-500mm ²)

Dimensions:

HS	13 mm
ID	19 mm
OD	25 mm
T	6 mm
L	79 mm

N	28 mm
W	36 mm
MOQ	25 .
Unit	pcs
Bolt dimension (metric)	12 .
Nominal cross section	150 mm ²
Series	KRF/KSF (10-500mm2)

Approvals:

Approved according to CE	Yes
Approved according to UKCA	Ja
Approved according to DNV	Yes

Compliance:

Conflict Minerals	Contain "Tin"
Extended Minerals	Contain "Copper"
PFAS	No PFAS
REACH	No SVHC (Latest. 05 Nov 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC001051 - Tube cable lug for copper conductors
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Cable lugs
Search Description	EFO2024V
Alternative SKU	150-12
E-no	E0845086

Logistic information:

Barcode	733117611958
Country of origin	CN
E-no	E0845086
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	25 .
Stock code	150-12
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se