



## TURN ONE INTO TWELVE

Multipoint locks multiply the number of mounting points.

This allows 12 padlocks to be mounted at once instead of just one, so that up to six people can independently secure the energy point against unauthorized reconnection.

## Technologies

- Vinyl coated high tensile steel
- Available with or without pry-resistant interlocking tabs for additional security
- Holds up to 6 padlocks
- Available with or without interlocking tabs to prevent unauthorized opening

## Operation and use

- Lock out power switches during maintenance
- Ideal for lockout applications where more than one safety padlock has to be attached

## Variants

- Shackle Clearance: 25 mm, 38 mm
- Large (width 60mm): H702, H712
- H711, H712: With interlocking tabs for added security

# Steel 1" (H701)



Security Tech Germany

Seite 2 von 2

## Technical data - Steel 1" (H701)

Depth	10 mm
Length	160 mm
Locking Points	12
Shackle Diameter	9 mm
Weight [g]	141 g
Width	45 mm
colour	red
EAN	4003318972683