

FEATURES

- **Non-Releasable Design:** Provides a secure and permanent fastening solution
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **High Tensile Strength:** Supports up to 34 kg, ensuring reliable performance in demanding conditions
- **UL 94 V-2 Fire Behaviour:** Meets fire safety standards, enhancing safety in critical environments
- **RoHS Compliant:** Environmentally friendly, adhering to global safety standards
- **Durable Nylon Material:** Offers excellent resistance to wear and tear
- **Wide Operating Temperature Range:** Functions effectively up to 85°C, suitable for various environments

RS PRO 368mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-060



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 368mm Nylon Cable Tie is designed for secure and efficient bundling of cables and wires. Ideal for use in various industrial and commercial applications, this non-releasable cable tie ensures a strong hold with a tensile strength of 34 kg, making it suitable for heavy-duty tasks.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	34 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	368 mm
Material	Nylon
Maximum Bundle Diameter	94 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---