


Features

- Fully flexible rubber pipe insulation
- Supplied in 2m lengths
- Manufactured without using CFC and HCFC gases
- Meets the requirements of Byelaw 49
- Suitable for frost protection, energy conservation and pipeline protection

RS PRO Black Nitrile Rubber Pipe Insulation, 42mm dia. x 19mm x 2000mm

RS Stock No.: 485-953



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Pipe Insulation



Product Description

The RS PRO 100mm Diameter Dual-Scale Pressure and Vacuum Gauge is a general purpose gauge suitable for all gaseous and liquid media that will not destruct the pressure system or attack copper alloy parts.

General Specifications

Pipe Diameter	42mm
Length	2m
Material	Nitrile Rubber
Thermal Conductivity	0.035 W/mK, 0.037 W/mK, 0.04W/mK
Wall Thickness	19mm
Colour	Colour
Note	Rubber Tube Insulation (Insultube) are supplied unslit

Operation Environment Specifications

Temperature Range		-40°C to +116°C	
Thermal Conductivity			
Mean Temp. °C	0	+20	+40
W/(m.K)	0.035	0.037	0.040

Approvals

Standards	BS476 Part 6: 1989
	BS476 Part 7: 1997, class 1