


Technical data sheet

Article number:

113-01810

T18MR



Product Group	1-piece fixing ties with mounting head for screws
Product Family	MR Series
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7ISP
Bundle Ø max.	20.0 mm
Bundle Ø min.	1.5 mm
Fixation Method	Fixing hole
Flammability	UL 94 V2
for Hole Ø (FH)	3.1 mm
Height (H)	4.2 mm
Length (L)	110.0 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Package Content packed in	pcs.
RoHS compliant	Yes
Specifications	CSA -C22.2 no. 62275
Thickness (T)	1.0 mm
UL-File Number	E64963
Variant	Inside Serrated
Width (W)	2.5 mm

HF ✓ RoHS ✓

c us