

WXT101N

Weathersafe Extreme Single Gang 13A Switched Socket

Features & Benefits

- Weathersafe 'Extreme' impact resistant solid ribbed lid
- Single gang switched socket – suitable for all 13 amp BS plugs
- Lockable cover facility
- Impact resistant housing
- Easy release lid catch
- Multiple M20 threaded screw-outs
- Power 'ON' neon indicator showing switch status
- Spacious design allowing full closure of lid with plug in position
- Complies with BS1363
- IP66 weatherproof rating



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface
Earth Class Rating	Class I
Operating Temperature	-5°C to 55°C
Ingress Protection Rating	IP66
Socket Outlet	Single Gang 13A BS Plug

Data sheet

WXT101N

Safety / Weathersafe Extreme

Switch type	Single Pole (Switched Socket)
Mounting Hole Centres (mm)	120 (Top/Bottom), 72 (Left/Right)
Cable Entry(s)	Back Entry, (Multiple M20 Threaded Screw-Outs Top/Bottom/Sides)

General

Weight (g)	430
Height (mm)	148
Width (mm)	108
Depth (mm)	75.5
Body Construction	Polycarbonate (Impact Resistant)
Product Colour	Grey
Accessories (Included)	x2 Cable Glands
EAN Number	5012483012734
Guarantee Period	3 Years

Data sheet

WXT101N

Safety / Weathersafe Extreme

Line Diagrams

