

Eaton CHM1DNU

Catalog Number: CHM1DNU

Eaton Bussmann series CHM modular fuse holder, 600V (UL), 690V (IEC), 30A (UL), 32A (IEC), 200 kAIC, Modular fuse holder, Single-pole - CHM1DNU



General specifications

Product Name	Catalog Number
Eaton Bussmann series CHM modular fuse holder	CHM1DNU
	EAN
	51712362603
UPC	Product Length/Depth
051712362603	0.001 mm
Product Height	Product Width
0.001 mm	0.001 mm
Product Weight	Compliances
109.333 g	Contact factory
	RoHS Compliant
Certifications	
Contact Manufacturer	

Product specifications

Used with

For use with 10 mm X 38 mm fuse

Type

Modular fuse holder

Amperage Rating

30A (UL), 32A (IEC)

Number of Poles

Single-pole

Operating temperature - max

120 °C

Operating temperature - min

-20 °C

Interrupt rating

200 kAIC

Wire size

#18-4 AWG

Voltage rating

600 V (UL), 690 V (IEC)

Resources

Declarations of conformity

[UKCA Modular fuse-holders](#)

[CE Modular fuse-holders](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - CHM1DNU](#)

Technical data sheets

[720147 10 x 38 mm Modular fuse holder](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia