



MEGA M 150-PP1

Bolt-On Fuse, Medium, 150A, Orange

Product Properties:

| | |
|----------------------------------|--------------|
| Explosion-proof | No |
| Release characteristic | Time-lag (T) |
| Rated voltage | 32 V |
| Optical defect indication | Yes |
| Type of current | DC |
| Colour code | Orange |
| Nominal voltage DC | 32 V |
| Max. continuous voltage DC | 32 V |
| Number of fuses | 1 . |
| Model | Other |
| Max. current (I _{max}) | 150 A |
| Nominal current | 150 A |
| Fuse type | Mega M |

Dimensions:

| | |
|------------------------------------------|--------|
| Width | 68 mm |
| MOQ | 1 . |
| Unit | pck |
| Rated voltage | 32 V |
| Mounting holes | M8 |
| Centre-to-centre distance of connections | 51 mm |
| Thickness | 9.7 mm |
| Length | 19 mm |

Approvals:

Compliance:

| | |
|--------------------------|-------------------------------|
| Conflict Minerals | Contain "Tin" |
| REACH | No SVHC (Latest. 04 Feb 2026) |
| RoHS | RoHS 3 (2015/863) |
| SCIP | Not Applicable |

Other information:

| | |
|---------------------------|---------------------------------|
| ETIM-Class | EC004122 - Strip fuse |
| ETIM-Release | DYNAMIC |
| Trademark | NECORE |
| Product Group | Bolt-on / Strip fuses - Pin-pac |
| Search Description | BOLT-ON SÄKRING, MEDIUM, 150A |
| Alternative SKU | MEGAM150-PP1 |

Logistic information:

| | |
|--------------------------|----------------------------------------------------------------------|
| Barcode | 733117610347 |
| Country of origin | MX |
| Item status | Stock item, normally in stock with reservation for in between sales. |
| MOQ | 1 . |
| Stock code | MEGA M 150-PP1 |
| Taric code | 85361090 |
| Unit | pck |

*We reserve the right to make technical changes and disclaim any typographical errors.