


M8 FEMALE 0° FIELD-WIREABLE SCREW TERM.

4-pol. 0,14...0.5mm²

Female straight M8, 4-pole Screw terminals Connection cross section: 0.14...0.5 mm²

Link to Product





Product may differ from Image




08631
max. 60 V
30 V
1.5 kV
max. 4 A
III
0.140.5 mm ²
3.55.0 mm
IP67 inserted and tightened (EN 60529)
III
3
-40+85 °C
PA
Gold plated bronze
45×12×12 mm
DE
85366990
4048879224505
27279221
1

The information in this brochure has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 01/22

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com



Female



Product may differ from Image

The information in this brochure has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 01/22

Murrelektronik GmbH | Falkenstraße 3 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com