

M230

 3,2 Kg

25

	art.	
024500230	M230	soft thermoformed tray with tool assortment
024510230	MV230	Soft thermoformed tray M230, empty

- n. 3 **30:** drift punches Ø 2-3-4 mm
- n. 6 **31:** pin punches Ø 2-3-4-5-6-8 mm
- n. 1 **32:** centre punch Ø 4 mm
- n. 1 **34:** flat chisels 150 mm
- n. 2 **35:** flat chisels, ribbed type 200-250 mm
- n. 1 **36:** cape chisels, standard type 125 mm
- n. 1 **1370:** engineer's hammer 500 g
- n. 1 **1390:** soft face hammer Ø 35 mm
- n. 1 **1692:** measuring tape 3 m
- n. 1 **1712TF:** telescopic magnet with flexible head
- n. 1 **1719BMA/Q:** 200 mm
- n. 1 **1719BMA/T:** 200 mm
- n. 1 **1719BMA/P:** 200 mm
- n. 1 **1719BMA/M:** 200 mm
- n. 1 **1719BMA/R:** 200 mm
- n. 1 **1737NX:** Steel wire brush
- n. 1 **1771:** snap - off blade utility knife 170 mm

