



PROHD

DS195FHD

19.5" LED Monitor Plastic Case

DS195FHD

Panel Type	19.5" 16:9 LED Panel
Case Type	Plastic
Maximum Resolution	1920(H) x 1080(V)
Active Display Area	434.88(H) x 238.68(V)mm
Pixel Pitch	0.2265 (H) x 0.221 (V)mm
Bezel Thickness	Left/Right 19.6mm, Top 22mm, Bottom 36.8mm
Contrast Ratio	3000:1
Brightness	250cd/m2
Response Time	5ms
Viewing Angle	178°/178° (H/V)
Display Colours	16.7M
Video Synchronization	Yes
PC Compatible Frequency	30-60KHz(H)/56-75KHz(V)
Adjustable Colour Temperature	9300K/6500K/5800K/User
Video Compatibility	NTSC/PAL
Aspect Ratio	16:9
VGA Auto Frequency correction	Yes
Speaker	2 x 2.5w
Number of Speakers	2
Sound Demodulation	Audio, Stereo
Mute	Yes
Work Humidity	5% - 90%
Work Temperature	-10° /+50°
Volume +/- Power On/Off	Yes



POWER

Power Supply	12V DC, 3 Amp
Voltage	AC110V - 240V 50/60 Hz
Power Consumption	<25W

OSD CONTROLS

Contrast, Brightness, Colour, Sharpness, Colour Temperature

OSD LANGUAGE

English, German, Italian, Spanish, French, Russian, Portuguese and Polish

ACCESSORIES

HDMI Cable, User Manual, Power Adapter, Power Lead

IN/OUT INTERFACE

Video Interface	1x BNC Composite In, 1x BNC Composite Out, 1x VGA, 1x HDMI
Audio Interface	1x PC Audio
Power Interface	DC in x 1
Termination	75 Ohms
Safety & EMC Certification	CE, RoHS, FCC-DOC
Vesa Standard Mount	75mm x 75mm
Stand Type	Desktop
Colour	Black
Button Position	Front Face, Bottom
Packing Dimension	530 x 120 x 420mm
NET Weight	3.3 Kg
GROSS Weight	3.8 Kg

