

## FEATURES

- 2 m and 5 m lead lengths
- 4 or 6 socket versions
- Low cost due to non-added surge protection
- Extension for both domestic and industrial purposes
- UK plug and sockets

## RS PRO 2m 4 Socket Type G - British Extension Lead, 250 V

RS Stock No.: 849-6137



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Brought to you by RS Pro, these convenient and efficient extension sockets are suitable for use in both the home and workplace. With both multiple socket versions available and a 2 m up to 10 m lead, the applications from each extension lead can range from powering TV's and phone chargers. All the way up to powering multiple industrial machines or appliances. All models are highly reliable and excellent quality.

## General Specifications

<b>Type</b>	Socket Strip
<b>Colour</b>	White
<b>Number of Sockets</b>	4
<b>Surge Protection</b>	No
<b>Switchable</b>	Yes
<b>RCD Protected</b>	No
<b>Application</b>	Mobile phone chargers, including those with a USB connectivity, Household entertainment (TVs, satellite boxes, routers etc.), Industrial machines and equipment, Office desks (Monitors, computers, phones), Any electrical device needed to be powered by the mains

## Electrical Specifications

<b>Mains Plug Type</b>	Type G - British BS1363
<b>Socket Type</b>	Type G - British
<b>Voltage Rating</b>	250V
<b>Current Rating (Unwound)</b>	13A
<b>Frequency</b>	50/60Hz

## Mechanical Specifications

Cable Length	2m
Cross Sectional Area	1.25 mm <sup>2</sup>

## Operation Environment Specifications

Operating Temperature	-20°C to +80°C
-----------------------	----------------

## Approvals

Compliance/Certifications	EN61340
---------------------------	---------



