

Features

- UL94V-2 flame rated, UL approved Nylon 66.
- Self-locking mechanism for secure fastening
- Max. operating temperature up to 85°C

RS PRO HVAS Duct Straps

RS Stock No.: 0656064



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A high-performance, super-strength nylon cable tie designed for secure and reliable bundling. Made from UL-approved Nylon 66 with a UL94V-2 flame rating, it offers excellent durability and resistance to wear, ensuring firm cable management. Low smoke and halogen-free, it is ideal for industrial, commercial, and domestic applications, withstanding temperatures up to 85°C

General Specifications

Series	Extra Strong Cable Ties
Type	Non-Releaseable
Colour	Natural
Material	Nylon 66
Finish	N/A
Application	Bundling wire together / Tightening labels to poles
Resistant To	N/A
UV Resistant	Yes
Minimum Operating Temperature	N/A
Maximum Operating Temperature	85°C
Fire Behaviour	Self-Extinguishing
Quantity	100

Mechanical Specifications

Length	940mm
Width	9.0mm
Tensile Strength	800N
Maximum Bundle Dia.	284mm

Approvals

Standards Met	UL RoHS
---------------	---------

