

Datasheet

RS Pro 4000W Fixed Installation DC-AC Power Inverter Pure sine, 24V dc / 230V ac

Stock number: 179-3345

RoHS 

Specifications:

Model	179-3345
Rated power	4000W
Surge power	8000W
Output voltage	230V
Output frequency	50Hz \pm 3
Output waveform	Pure sine wave
USB port	5V 2.1A
Input voltage	24V
Dimension (LxWxH)	543x230x107.7mm
N.W/unit	8980g

Features:

- Anodized aluminum case provides durability & max heat dissipation
- Two LED indicators on the front panel shows the working and failure state
- ON/OFF switch control the inverter by hand
- The inverter is compact, light weight and east to operate.
- Protections: overheat, overload, low-voltage alarm & shutdown, over-voltage, short circuit, reverse polarity
- Soft start
- Auto. Reset after being in protected
- Universal UK/Euro output socket.

